


S-Quad Anti-Ligature Base

The S-Quad Anti-Ligature ceiling mounted base provides additional safety to occupants within secure facilities.

Assembly Layout



Description

This base has been designed to provide additional safety within buildings that accomodate people who are at risk.

Sdal patent 2528032A

KEY FEATURES

- Built in magnetic switch provides loop continuity when multiple items are removed.
- Anti tamper lip to prevent storage of contraband between base and detector.
- Simple design and easy to install.
- Certified to 6.4kg release load.
- Easy to reinstate the device if removed.
- Approved for in-cell detection by National Offender Management Services (NOMS) in England.
- Labour saving installation as no need for a T-Breaker to maintain loop continuity.

S-Quad Anti-Ligature Base

Technical Specifications

SPECIFICATION	
Release load	6.4kg
Weight of device	0.16kg
Dimensions	138mm diameter by 30mm height

DESCRIPTION	ORDER CODES
Anti-Ligature Base	ALD302

Design consideration:

Loop Capacity: To ensure performance of the loop is not compromised, we recommend that loop resistance is monitored during and after commissioning using the Vigilon Loop Diagnostics Tool. It may be necessary to limit the quantity of Anti-Ligature devices on the loop.

Honeywell Gent

140 Waterside Road
Hamilton Industrial Park,
Leicester, LE5 1TN
Telephone: 0203 409 1779
E-mail: gentenquiry@honeywell.com
www.gent.co.uk

Content subject to change without
prior notice

© 2019 Honeywell International Inc.

Honeywell
GENT