

Midas[®] SENSOR CARTRIDGE SPECIFICATIONS

Carbonyl Sulfide (COS) MIDAS-X-COS



Gas Measure	Carbonyl Sulfide (COS)
Cartridge Part Number	MIDAS-X-COS 2 year extended warranty
Sensor Technology	4 electrode electrochemical cell
Measuring range (ppm)	COS 0-100 ppm
Minimum Alarm 1 Set Point	10 ppm
Repeatability	< ± 30 % of full scale
Linearity	< ± 30 % of full scale
Response time t62.5	≤ 60 seconds
Sensor Cartridge Life Expectancy	≥ 24 months under typical application conditions
Operating temperature	0 °C to + 40 °C (32 °F to 104 °F)
Effect of Temperature	
Zero	< ± 10 ppm (at 10 °C to 30 °C)
Sensitivity	< ± 30 % of full scale (at 10 °C to 30 °C)
Operating humidity	15-90 %RH (Sensor Datasheet)
Effect of Humidity	
Zero	< ± 10 ppm (at 45 %RH)
Sensitivity	< ± 30 % of full scale (at 45 %RH)
Operating Pressure	90 – 110kPa (Sensor Datasheet)
Effect of Position	No effect in typical application
Long Term Drift	
Zero	< ± 10 ppm
Sensitivity	< ± 30 % of full scale
Calibration Gas	Carbonyl Sulfide (50 ppm COS)
Challenge Gas (Bump Test)	Carbonyl Sulfide (50 ppm COS)
Warm Up Time	≤ 60 minutes
Storage Temperature	+3 °C to +20 °C (+37 °F to +68 °F) (Sensor Datasheet)

The sensor data listed is based on ideal test environment; observed performance may vary based on the actual monitoring system and the sampling conditions employed.

Cross Sensitivities

Each Midas[®] sensor is potentially cross sensitive to other gases and this may cause a gas reading when exposed to other gases than those originally designated. The table below presents typical readings that will be observed when a new sensor cartridge is exposed to the cross sensitive gas (or a mixture of gases containing the cross sensitive species).

Gas / Vapor	Chemical Formula	Concentration Applied (ppm)	Reading (ppm COS)
Carbon Monoxide	CO	50	≥100
Hydrogen Sulfide	H ₂ S	15	<100
Sulfur Dioxide	SO ₂	5	9
Nitrogen Dioxide	NO ₂	5	-15
Chlorine	Cl ₂	1	-1.5
Hydrogen	H ₂	100	<100
Hydrogen Cyanide	HCN	10	15
Hydrogen Chloride	HCl	5	0
Ethylene	C ₂ H ₄	100	<100
Nitric Oxide	NO	35	30
iso-Propyl Alcohol (IPA)*	C ₃ H ₇ OH	500	0

*IPA filter (1830K0080) is required where a sensor cartridge can be exposed to the concentrated IPA vapor.

Find out more

www.honeywellanalytics.com

Toll-free: 800.538.0363

Please Note:

While every effort has been made to ensure accuracy in this publication, no responsibility can be accepted for errors or omissions. Data may change, as well as legislation, and you are strongly advised to obtain copies of the most recently issued regulations, standards, and guidelines. This publication is not intended to form the basis of a contract.