








Product Family
Miller Rope Grabs and Vertical Lifelines

Rope Grabs move easily up and down vertical lifelines providing continuous fall protection. Trailing models offer complete hands-free operation. In the event of a fall, Miller rope grabs lock quickly.



Product Numbers & Ordering Information

Product Numbers	Details
 194R-2/30FTWH	Rope Lifeline 30-ft. length, 1 thimble and 1 carabiner, 5/8-in. nylon
 194R-2/50FTWH	Rope Lifeline 50-ft. length, 1 thimble and 1 carabiner, 5/8-in. nylon
 195R-2/50FTWH	Rope Lifeline 50-ft. length, 2 thimbles, 5/8-in. nylon
 198RLS-2/25FTWH	Rope Lifeline 25-ft. length, 1 locking snap hook and 1 loop, 5/8-in. nylon
 198RLS-2/50FTWH	Rope Lifeline 50-ft. length, 1 locking snap hook and 1 loop, 5/8-in. nylon
 201RLS-2/50FTWH	Rope Lifeline 50-ft. length, 2 locking snap hooks, 5/8-in. nylon
 300L/100FTBL	Rope Lifeline 100-ft. length, 5/8-in. dia. polypropylene blend, 1 snap hook and 1 loop

Miller Rope Grabs and Vertical Lifelines



300L/25FTBL

Rope Lifeline

25-ft. length, 5/8-in. dia. polypropylene blend, 1 snap hook and 1 loop



300L/30FTBL

Rope Lifeline

30-ft. length, 5/8-in. dia. polypropylene blend, 1 snap hook and 1 loop



300L/50FTBL

Rope Lifeline

50-ft. length, 5/8-in. dia. polypropylene blend, 1 snap hook and 1 loop



300L/75FTBL

Rope Lifeline

75-ft. length, 5/8-in. dia. polypropylene blend, 1 snap hook and 1 loop



8172/U

MicroLoc Trailing Wire Rope Grab

Stainless steel; for use with 5/16-in. wire rope



8173/U

MicroLoc Trailing Rope Grab

Stainless steel; for use with 5/8-in. synthetic rope



8174/U

Manual Rope Grab

Stainless steel; w/O-ring



8174MLS4/4FTYL

Manual Rope Grab

Stainless steel; attached 4-ft. Manyard lanyard w/1 locking snap hook; for use with 5/8-in. or 3/4-in. synthetic rope



8174MLS6/6FT

Manual Rope Grab

Stainless steel; attached 6-ft. Manyard lanyard w/1 locking snap hook; for use with 5/8-in. or 3/4-in. synthetic rope



8175/U

Trailing Rope Grab

Stainless steel; w/O-ring; for use with 5/8-in. synthetic rope



8175SLS/3FTYL

Trailing Rope Grab

Stainless steel; attached 3-ft. SofStop lanyard w/1 locking snap hook; for use with 5/8-in. synthetic rope



8175-Z7/

ANSI Z359-2007 Compliant Trailing Rope Grab

Stainless steel; w/O-ring; anti-panic feature; for use with 5/8-in. synthetic rope



8757LS/YL

Manual Rope Grab

Stainless steel; w/O-ring; for use with 5/8-in. synthetic rope; attached 24-inch SofStop

Overview

Key Features

- Compact design; corrosion-resistant stainless steel construction.
- Lightweight and easy to use.
- Miller rope grabs are designed for use with 5/8-inch (16mm) synthetic rope lifeline with a minimum tensile strength of 5,000 lbs. (22kN), secured to an anchorage independent of the worker's platform.
- Standard lifeline lengths are 25 feet (7.6m), 50 feet (15m), 75 feet (23m), and 100 feet (30m); additional lengths are available.
- Wire rope grabs are designed for use with 5/16-inch (8mm) galvanized or stainless steel wire rope lifelines.

Recommended Industries/Use

- Agriculture
- Construction
- Government
- Manufacturing
- Municipal Services
- Oil and Gas
- Utilities

Hazards

- Confined Space
- Fall from height

Regulations

- Meets all applicable OSHA, ANSI and CSA standards

Warranty Information

We sincerely believe that our fall protection equipment is the best in the world. Our products endure rigorous test to ensure that the fall protection equipment you trust is manufactured to the highest standards. Miller fall protection products are tested to withstand normal wear and tear, but are not indestructible and can be damaged by misuse. Our Limited Lifetime Warranty does not apply to normal wear and tear or abusive treatment of the product. In the unlikely event that you should discover defects in either workmanship or materials, under our Limited Lifetime Warranty, we will repair or replace the product at our expense. If a replacement is necessary and your product is no longer available, a comparable product will be substituted. Should a product issue surface, contact us at 800/873-5242. Manufacturing specifications are subject to change without notice.

Literature & Documents

Miller Rope Grabs & Vertical Lifelines Manual - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/16592/1033.aspx

Miller Rope Grabs and Vertical Lifelines Product Instruction Manual

SP 396 300L Rope Lifeline Spec Sheet - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/16593/1033.aspx

SP396 300L Rope Lifeline Product Specification Sheet

SP387 8174 Rope Grab - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/42962/1033.aspx

SP387 8174 Rope Grab Product Specification Sheet

SP388 MicroLoc Rope Grabs - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/42963/1033.aspx

SP388 MicroLoc Rope Grabs Product Specification Sheet

SP389 8175 Rope Grab USA - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/42964/1033.aspx

SP389 8175 US Rope Grab Product Specification Sheet

SP390 Rope Grab CANADA - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection

[/Rope_Grabs___Vertical_Lifelines/42965/1033.aspx](#)

SP390 Canadian Rope Grab Product Specification Sheet

SP391 Rop Grab CANADA - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/42966/1033.aspx

SP391 Canadian Rope Grab Product Specification Sheet

SP417 195R Series - US

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/Rope_Grabs___Vertical_Lifelines/42967/1033.aspx

SP417 195 Series Product Specification Sheet

Training & Proper Use

Proper product training and professional fall protection training is recommended. Refer to Product Use Instructions enclosed with products.

Additional Information

800/873-5242 or 814/423-2118 email: millertechexpert@sperian.com

Technical Support

Contact Miller Technical Service at 800/873-5242 or 814/423-2118 email: millertechexpert@sperian.com