

Systevo Workstation (230 VAC) System-Release V11 Standard



Features:

- Universal housing, as desktop or installation frame for 19" rack
- Mainboard with Quad-Core µP J19xx, 2 GHz or equivalent, min. 4 GB RAM
- 1* Solid-State HDD (SSD) min. 128 GB
- drive DVD+-RW, VGA graphics card
- 4* RS232, 1* parallel, USB
- 2* LAN Ethernet (min 10/100 MBit)
- Mouse and keyboard, radio-controlled clock DCF-77
- Hardened operating system Windows 10 IoT Entry
- Backup/user software
- Continuous operation: 24/7

Part-No.: 765M350

System Workstation for configuration, display, operation and logging for Systevo Call Ackermann, equipped with system release V11.

System license required, depending on the system functions/size. Optionally as an interface to third-party systems, such as DECT system, fire detection system.

Comprised of a high-quality system computer with keyboard, mouse, SSD, DVD+/-RW, interfaces (RS232, LAN).

Equipped with user software with system release V11:

Configuration tool Systevo Call AckermannAllocation of the room configurationDefinition of functions/parameters of the call system in accordance with DIN VDE 0834-1: 2016-06Set-up of the call types, call type groups, call type upgradesSet-up of the VoIP/SIP channel for mobile call querying via DECT/WIFI (separate license/SIP license required)Configuration of input/output events for controlling external systems: Light/blind/TVSetting of radio and TV channelSystem management tools, database management systemNetwork functions for system accessesFreely configurable services (interconnection)Allocation of timed servicesSelection of call type groups for servicesConfiguration of the volume of the acoustic call forwarding (day/night)Definition of target-oriented forwarding between stations (call types)Freely configurable announcement functionsSelection of destinations for announcementsFault monitoring and reporting (in accordance with DIN VDE 0834-1: 2016-06)Graphic / tabular display of messages according to priority/call type/timePresence/call messagesAccess control via user ID (if necessary)Output of the data on a printer

Following Functions only in combination with a master station:

Call retrieval/, cancellationDialing up of rooms / making announcements to selected destinationsEntry and administration of patient data, incl. administration of the bed occupation (manual)

Optional:

Message transmission to a wireless messaging system (e.g. WIFI-/DECT system or Paging)Freely configurable recipient addresses for messages from groups of the call systemDefinition of the display format for the messages to be transmittedSet-up of various services (e.g. day, night service)Allocation of repetition times, acoustic call tones, etc.

Operating voltage 230

Power consumption 100 W max.

Ambient temperature 10 °C ... 35 °C

Storage temperature 0 °C ... 50 °C

Air humidity < 20 %

Weight approx. 6,5 kg (workstation)

Dimensions W: 420 mm H: 325 mm D: 95 mm workstation



EN 55022/55024/61000-3/60950-1 2004/108/EC, 2006/95/EC, 2005/32/EC 2003/95/EC, Regulation (EC)1275/2008 Product not available anymore. Successor: 765M440 with System-Release 12.

Novar GmbH a Honeywell Company Forumstr. 30 41468 Neuss www.ackermann-clino.com info@ackermann-clino.com