

Call unit with call push-button and 2 monitored sockets

**Part-No.: 73075E**

Call unit for call initiation to connect to an electronic module or room terminal via a passive input. Mobile call units, such as pear and multiple push-buttons, are connected to the 7-pin plugs. Additional 6-pin plugs for connecting a medical unit (e.g. Infusiomat infusion pump) with alarm contact. Superordinate room identification signal displayed after call activation. Monitoring of connected call units (call circuit monitoring).

Mounting	in flush-mounting box, DIN 49073
Type of protection	IP40, when installed incl. suitable cover plate
Dimensions	W: 71 mm H: 71 mm

Features:

- 1 call push-button
- 1 LED orientation and reassurance lamp (red)
- 1 monitored 7-pin plug
- 1 monitored 6-pin plug



Call push-button, threadless connection terminals

Accessories:

88881J3N Cover plate with push-button (red) and units with 2 sockets